



Low Voltage Distribution Transformer - Single Phase, 190/208/220/240 X 380/416/440/480 - 120/240V, 10kVA

By Acme Electric
Catalog # [TF279265S](#)



*Representative Image

Low Voltage Distribution Transformer - Single Phase,
190/208/220/240 X 380/416/440/480 - 120/240V, 10kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

CE Compliant	CE Marked
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	190 / 208 / 220 / 240 X 380 / 416 / 440 / 480 V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503420935
Winding Material	AL
kVA	10

Dimensions

Dimensions	10.84 in x 13.5 in x 15.19 in
Height	15.19 in
Length	10.84 in
Weight	125 lb
Width	13.5 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	190/208/220/240 X 380/416/440/480 V

Certifications and Compliance

CE Compliant	CE Marked
CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Product Assets

[3D Models - Group_24](#)
[Brochures - General Purpose Dry-Type Distribution Transformers](#)
[Brochures - International Transformers](#)
[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Engineering Drawing - TF279265S](#)
[Installation Manuals - Acme Electric Manual A](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
ACME_TF279265S_SPEC | REV 3/2023