



FEATURES

- Slim design, less than 5" wide and only 4" deep
- Smooth white acrylic diffuser for soft even illumination
- White injection molded decorative plastic ends hold diffuser in place. Easily removable for lamp access
- Heavy gauge steel die formed housing with heat sink embossments behind ballast for cooler operation and longer life

PROJECT INFORMATION

Project Name

Type

Catalog No.

Date

BALLASTS

Energy efficient, thermally protected, automatic resetting, Class P, high power factor, sound rated A, unless otherwise specified. CEE NEMA Premium compliant.

ELECTRICAL

Standard class "P", thermally protected, auto-resetting HPF ballast, sound rated A, CEE NEMA Premium compliant. All ballast leads extend a minimum of 6" through access location. NEC/ETC-compliant ballast disconnect is standard.

FINISH

White painted parts are coated with a five-stage phosphate bonding process and covered after fabrication with a minimum 90% reflective gloss baked enamel.

SHIELDING

100%opal acrylic extrusion

CERTIFICATION

All luminaires are built to UL and ENEC standards and bear the appropriate UL and ENEC labels. Emergency fixtures are built to UL and ENEC standards.

ORDERING INFORMATION

EXAMPLE AD4-132-EU

MODEL	LENGTH	NO. OF LAMPS	LAMP TYPE	BALLAST	VOLTAGE	OPTIONS
AD Corridor Light	2' 3' 4'	1 0 or 2	14 2', T5: 14 Watt 17 2', T8: 17 Watt 21 3', T5: 21 Watt 24 2', T5HO: 24 Watt 25 3', T8: 25 Watt 28 4', T5: 28 Watt 32 4', T8: 32, 30, 28 or 25 Watt 39 3', T5HO: 39 Watt 54 4', T5HO: 54 or 51 Watt	E (1 or 2-Lamp) Electronic T8, Instant Start EP (1 or 2-Lamp) Electronic T5 or T8, Programmed Start For a specific ballast vendor, show as option.	U 120V-277V 347 347V	GLR Fast Blow Fuse EL Emergency Battery Pack PAF Paint After Fabrication
ACCESSORIES (ORDER SEPARATELY)						
ITB4 T-Bar Hanger						
S18 18" Stem, Canopy						
SS18 18" Swivel Stem - 45° Swivel						