



* Representative image

ALRB055TBC

by Acme Electric

Catalog ID: ALRB055TBC

Prop65_Cancer&Reproductive

AC Line Reactor - Three Phase, 240 Volts 6% Z - 480 Volts 3% Z - 600 Volts 2.4% Z, 401 uH, 55 A, CE Marked

- Protects from damaging voltage drop
- Eliminates nuisance tripping
- Reduces surges and spike currents
- Longer life for motors and solid state components

Product Details

General

CE Compliant	CE Marked
Inductance	401 uH
Inductance Range	301-450 uH
Max Temperature Rise	115 Degrees Celsius
Motor Power	40 HP
Mounting Hole Width	3.60 in. (9.1 mm)
Primary Voltage	240V / 480V / 600V
Product Category	AC Line Reactor
Reactor Current	55 A
UL Insulation Class	180°C
UPC	047503000458
Winding Material	CU

Dimensions

Height	7 in
Length	4.5 in
Weight	22 lb
Width	9 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240/480/600 V

Certifications and Compliance

CE Compliant	CE Marked
CSA Standard	C22.2 No 66

UL Standard	UL 506
-------------	--------