



* Representative image

ALRC025TBC

by Acme Electric

Catalog ID: ALRC025TBC

Prop65_Cancer&Reproductive

AC Line Reactor - Three Phase, 240 Volts 10% Z - 480 Volts 5% Z - 600 Volts 4% Z, 1470 uH, 25 A, CE Marked

- Protects from damaging voltage drop
- Eliminates nuisance tripping
- Reduces surges and spike currents
- Longer life for motors and solid state components

Product Details

General

CE Compliant	CE Marked
Inductance	1470 uH
Inductance Range	751+ uH
Max Temperature Rise	115 Degrees Celsius
Motor Power	15 HP
Mounting Hole Width	2.00 in. (5.1 mm)
Primary Voltage	240V / 480V / 600V
Product Category	AC Line Reactor
Reactor Current	25 A
UL Insulation Class	180°C
UPC	047503089187
Winding Material	CU

Dimensions

Height	4.75 in
Length	4.5 in
Weight	13 lb
Width	6.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240/480/600 V

Certifications and Compliance

CE Compliant	CE Marked
CSA Standard	C22.2 No 66

UL Standard	UL 506
-------------	--------