



# 34.5kV, 200kV LIW, 600A, ALTD Switch with Loadbuster Hooks.

by CHANCE Utility  
Catalog ID: ALTD06200RC

34.5kV, 200kV LIW, 600A, Line Tension Disconnect Switch with Loadbuster Hooks.



\* Representative image

## Product Details

### General

Blade Type	Solid Copper (two blade truss-member)
Color - Insulator	Dark Gray
Contact	Silver, Copper
Insulator Type	ESP™ Polymer
Tension Range	15000 lb
UPC	096359005100

### Dimensions

Weight	15.68 lb
--------	----------

### Electrical Ratings

Arc Distance - Dry	15.3" (388.6mm)
BIL	200 kV
Creep and Leakage Distance	31.4" (797.6mm)
Current Overload - 8hr Emergency	1080 A
Current Rating	600 A
Dead-Ending Rating - Working Load	15,000 Lbs
Reference Voltage Limit - Minimum	34.5kV
Temperature Rise - Max. at 600A	28°C
Voltage - Maximum	38 kV
Withstand Current - Short Time (1 sec)	25kA, symmetrical
Withstand Current - Short Time (10 cycles)	40kA, assymetrical

### Certifications and Compliance

Industry Standard(s)	All Applicable ANSI/IEEE Standards
----------------------	------------------------------------

### Logistics

Pallet Quantity	24 EA
Standard Package	1

For further technical assistance, please contact us

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscshubbell.com](mailto:hpscshubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)