

HUBBELL Power Systems

Strain Clamp, Snubbing

By ANDERSON

Catalog # [805002000](#)

"Bolted Stud Connectors, Connecting Stud to Cable, Stud Dia./Thd.- 1-1/4"-12, Conductor Range: AAC-250-400 MCM, ACSR- 4/0-336.4 MCM, Dia.- 0.563"-0.744", Material: Castings- Aluminum Alloy, Hardware- Aluminum Alloy"



General

Fitting Type	None
Material	Ductile Iron
Number of Pad Holes	0
Product Category	Strain Clamp
Strength Rating - Ultimate	8000 lb
Body	
Tension Range	0 lb
Type	Bolted
UPC	096359252375

Dimensions

Dimensions	4.330 in x 1.190 in x 0.730 in
Height	0.73 in
Length	4.33 in
Messenger Diameter Range	0 - 0
Take Up	0 in
Thickness - Pad	0 in
Total Adjustment	0 in
Weight	1.684 lb
Width	1.19 in

Conductor Related

Conductor Diameter - Maximum	0.38 in
Conductor Diameter - Minimum	0.12 in
Conductor Diameter Range	0.12 - 0.38
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Logistics

Pallet Quantity	810
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)
[Catalogs - Distribution Connectors](#)



A Hubbell brand