

Clevis Eye, Long

By ANDERSON
Catalog # [829102000](#)

Clevis Eye Link, Ductile Iron, Length 10", Clevis Opening 0.813" wide & 1.125" deep, Clevis Pin 0.625" dia, Eye is 0.625" wide, Eye Hole 0.688" dia, UTS 20,000 lb



*Representative Image

Features

- "BNK" suffix if added replaces clevis pin & cotter pin with bolt, nut & cotter pin

General

EU RoHS Indicator	No
Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Series	CEEL Series
Strength Rating - Ultimate	20000 lb
Type	Extension Links
UPC	096359252429

Dimensions

Diameter - Eye Hole	0.625 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	10 in
Weight	4.018 lb

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)