

Deadend, Straight Line. Ductile, Copper, CopperWeld, Alumoweld. Conductor Range 0.65 - 1.25 in, Fitting: None

By ANDERSON
Catalog # [876822000](#)



*Representative Image

Deadend, Straight Line. Ductile, Copper, CopperWeld, Alumoweld. Conductor Range 0.65 - 1.25 in, Fitting: None

Features

- For use with copper and CopperWeld phase conductor
- Magnetic induction heating will occur
- For dead ending static wire
- Add "S" for socket OR "C" for clevis fitting

General

Catalog Number	876822000
Fitting Type	None
Material	Ductile Iron; Steel
Material - Body	Ductile Iron
Material - Hardware	Galvanized Steel
Material - Keeper	Ductile Iron
Product Category	Straight Line
Strength Rating - Ultimate	10000 lb
Body	
Style	87600 - Deadend, Straight Line
Type	Bolted
U-Bolts	2 in
UPC	096359252573

Dimensions

Clevis Opening	0.75 in
Diameter - Bolt	0.5 in
Diameter - Pin	0.625 in
Weight	5.39 lb

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Conductor Compatibility	ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-
-------------------------	--

18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Parakeet-556.5-24/7;ACSR-Dove-556.5-26/7;ACSR-Eagle-556.5-30/7;ACSR-Peacock-605-24/7;ACSR-Squab-605-26/7;ACSR-Teal-605-30/19;ACSR-Kingbird-636-18/1;ACSR-Swift-636-36/1;ACSR-Rook-636-24/7;ACSR-Grosbeak-636-26/7;ACSR-Egret-636-30/19;ACSR-Flamingo-666.6-24/7;ACSR-Gannet-666.6-26/7;ACSR-Stilt-715.5-24/7;ACSR-Starling-715.5-26/7;ACSR-Redwing-715.5-30/19;ACSR-Coot-795-36/1;ACSR-Cuckoo-795-24/7;ACSR-Drake-795-26/7;ACSR-Tern-795-45/7;ACSR-Condor-795-54/7;ACSR-Mallard-795-30/19;ACSR-Ruddy-900-45/7;ACSR-Canary-900-54/7;ACSR-Rail-954-45/7;ACSR-Cardinal-954-54/7;ACSR-Ortolan-1033.5-45/7;ACSR-Curlew-1033.5-54/7;ACSR-Brahma-203.2-16/19;AAC-Daffodil-350-19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37;AAC-Orchid-636-37;AAC-Flag-700-61;AAC-
--

Violet-715.5-37;AAC-
Nasturtium-715.5-61;AAC-
Cattail-750-61;AAC-Arbutus-
795-37;AAC-Lilac-795-61;AAC-
Cockscomb-900-37;AAC-
Snapdragon-900-61;AAC-
Magnolia-954-37;AAC-
Goldenrod-954-61;AAC-
Camellia-1000-61;AAC-
Bluebell-1033.5-37;AAC-
Larkspur-1033.5-61;AAC-
Marigold-1113-61;ACAR-653.1-
12/7;ACAR-739.8-18/19;ACAR-
853.7-30/7;ACAR-1024.5-
30/7;ACAR-1081-18/19;ACAR-
1109-30/7;ACAR-1172-
30/7;ACAR-1172-18/19

Conductor Diameter -	1.25
Maximum	
Conductor Diameter - Minimum	0.65
Conductor Diameter Range	0.65 - 1.25

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	300
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Specifications - 876822000](#)



A Hubbell brand