

## Strain Clamp, Snubbing

By ANDERSON  
Catalog # [885002000](#)

"Bolted Stud Connectors, Connecting Stud to Cable, Stud Dia./Thd.- 1-1/4"-12, Conductor Range: AAC-250-400 MCM, ACSR- 4/0-336.4 MCM, Dia.- 0.563"-0.744", Material: Castings- Aluminum Alloy, Hardware- Aluminum Alloy"



### General

EU RoHS Indicator	No
Fitting Type	None
Material	Ductile Iron
Product Category	Strain Clamp
Strength Rating - Ultimate Body	10000 lb
Type	Bolted
UPC	096359252672

### Dimensions

Messenger Diameter Range	0 - 0
Weight	2.350 lb

### Conductor Related

Conductor Diameter - Maximum	0.5 in
Conductor Diameter - Minimum	0.2 in
Conductor Diameter Range	0.2 - 0.5

### Logistics

Pallet Quantity	800
-----------------	-----

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)