

Socket Y-Clevis

By ANDERSON
Catalog # 942773001

Socket Y-clevises are used to connect yoke plates or associated hardware to ball and socket insulators. The ben bolt in the YOsection provides an additional point of articulation within an assembly.

Features

- Ultimate strength is 50,000 lbs. (222 kN)
- 0.875" Curved Bolt Diameter
- Material: Body - galvanized ductile iron, Hardware - galvanized steel, Cotter Pin - stainless steel
- For use with ANSI class 52-8 & 52-11 insulators per ANSI Spec. C29.2-71.
- Shield nut can be supplied by adding suffix "SN" to catalog number. Example: 942773001SN.

General

Catalog Number	942773001
Material	Ductile Iron
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	SYC Series
Strength Rating - Ultimate	50000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359253143
With Sphere Nut	No

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in



*Representative Image

Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	2.938 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	4.9 lb

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	480
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Specifications - 942773001](#)