

Bus Support, Aluminum Bolted

By ANDERSON
Catalog # [ACS133](#)



Aluminum alloy bus support for aluminum cable to insulator.

Features

- Conductor Range: 600 - 1250 MCM AAC and 556.5 - 1113 ACSR
- Cable Diameter Ranges: Small Groove - 0.870 - 1.125 inches and Large Groove - 1.125 - 1.293 inches
- Bolt Circle Diameter - 3 inch
- Material: Castings - 356-T6 aluminum alloy, Clamping Hardware - aluminum alloy
- Clamping bolts have hex-stops for one-wrench installation
- Provided with four galvanized steel HH bolts, lock washers and flat washers to mount to insulator cap.
- Cap screws are supplied for upright mounting.

General

Catalog Number	ACS133
Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Material - Mounting Hardware	Galvanized Steel
Number of Ground Braid Lug	0
Holes	
Type	Bus Support, Cable to Insulator
UPC	096359280361

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Bolt Circle	3 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	2.45 lb

Electrical Ratings

Maximum Current Rating Amps	0
Continuous	

Conductor Related

Conductor Compatibility	ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Parakeet-556.5-24/7;ACSR-Dove-556.5-26/7;ACSR-Eagle-
-------------------------	--

	556.5-30/7;ACSR-Peacock-605-24/7;ACSR-Squab-605-26/7;ACSR-Teal-605-30/19;ACSR-Kingbird-636-18/1;ACSR-Swift-636-36/1;ACSR-Rook-636-24/7;ACSR-Grosbeak-636-26/7;ACSR-Egret-636-30/19;ACSR-Flamingo-666.6-24/7;ACSR-Gannet-666.6-26/7;ACSR-Stilt-715.5-24/7;ACSR-Starling-715.5-26/7;ACSR-Redwing-715.5-30/19;ACSR-Coot-795-36/1;ACSR-Cuckoo-795-24/7;ACSR-Drake-795-26/7;ACSR-Tern-795-45/7;ACSR-Condor-795-54/7;ACSR-Mallard-795-30/19;ACSR-Ruddy-900-45/7;ACSR-Canary-900-54/7;ACSR-Rail-954-45/7;ACSR-Cardinal-954-54/7;ACSR-Ortolan-1033.5-45/7;ACSR-Curlew-1033.5-54/7;ACSR-Bluejay-1113-45/7;ACSR-Finch-1113-54/19;AAC-Meadowsweet-600-37;AAC-Orchid-636-37;AAC-Flag-700-61;AAC-Violet-715.5-37;AAC-Nasturtium-715.5-61;AAC-Cattail-750-61;AAC-Arbutus-795-37;AAC-Lilac-795-61;AAC-Cockscomb-900-37;AAC-Snapdragon-900-61;AAC-Magnolia-954-37;AAC-Goldenrod-954-61;AAC-Camellia-1000-61;AAC-Bluebell-1033.5-37;AAC-Larkspur-1033.5-61;AAC-Marigold-1113-61;AAC-Hawthorn-1192.5-61
Conductor Diameter - Maximum	1.293 in
Conductor Diameter - Minimum	0.87 in

Conductor Diameter Range	0.87 - 1.293
Conductor Type	- AAC - ACSR

Pallet Quantity243

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Product Assets

- Catalogs - Substation Connectors (SA)
- Specifications - ACS133
- Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products
- Video - Hubbell Power Systems Quick Ship

Logistics

