

HUBBELL

Power Systems

Deadend, Straight line, Stirrup Clamp, AAC, AAAC, ACAR, ACSR, Conductor Range 0.46 - 0.7 in, Fitting: None

By ANDERSON
Catalog # [ADES70N](#)



Deadend, Straight line, Stirrup Clamp, AAC, AAAC, ACAR, ACSR, Conductor Range 0.46 - 0.7 in, Fitting: None

Features

Add "S" for socket OR "C" for clevis fitting options

General

Fitting Type	None
Material	Aluminum
Material - Body	356 T6 Aluminum Alloy
Material - Hardware	Galvanized Steel
Material - Keeper	356 T6 Aluminum Alloy
Product Category	Straight Line
Strength Rating - Ultimate	8000 lb
Body	
Style	ADES
Type	Bolted
U-Bolts	2 in
UPC	096359281047

Dimensions

Clevis Opening	0.75 in
Diameter - Bolt	0.5 in
Diameter - Pin	0.625 in
Take Up	0 in
Weight	2.94 lb

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Daffodil-350-19;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18
Conductor Diameter - Maximum	0.7
Conductor Diameter - Minimum	0.46
Conductor Diameter Range	0.46 - 0.7

Logistics

Pallet Quantity	180
-----------------	-----

Product Assets

[Catalogs - Distribution Connectors](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - Aluminum Dead-End Stirrup-Strain Clamp \(C-1689\)](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-ADES70N-SPEC-EN | REV 6/2024