


**Deadend, Straight line, #6 (7 STR) -
3/0 (19 STR) AL, #6 (6/1) - 2/0
(6/1) ACSR**

By ANDERSON
Catalog # [ADS47N](#)



*Representative Image

Deadend, Straight line, #6 (7 STR) - 3/0 (19 STR) AL, #6 (6/1) - 2/0 (6/1) ACSR, Conductor Range 0.18 - 0.47 in, Fitting: None.

Features

- Add "S" for socket or "C" for Clevis fitting options, Extra length for greater insulator clearance
- Spring Loaded, side opening keeper for easy installation
- Single 1/2" U-Bolt for use with hand or hydraulic tool installation
- RUS Listed

General

Catalog Number	ADS47N
Fitting Type	None
Material	Aluminum
Material - Body	356 T6 Aluminum Alloy
Material - Hardware	Galvanized Steel
Material - Keeper	356 T6 Aluminum Alloy
Material - Pin (Cotter)	#302 Stainless Steel
Product Category	Straight Line
Strength Rating - Ultimate	15000 lb
Body	
Style	ADS
Type	Bolted
U-Bolts	2 in
UPC	096359281412

Dimensions

Diameter - Bolt	0.5 in
Diameter - Pin	0.625 in
Length	5.38 in
Weight	1.1 lb
Width	0.69 in

Conductor Related

Conductor Compatibility

ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Sparrow-2-6/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18

Conductor Diameter - Maximum	0.47
Conductor Diameter - Minimum	0.18
Conductor Diameter Range	0.18 - 0.47

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	900
-----------------	-----

Product Assets

[Catalogs - Distribution Connectors](#)
[Literature - Deadends For Overhead Connections](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - Deadend, Clamp \(C-8253\)](#)
[Specifications - ADS47N](#)