

**Deadend, Straight line, Spring  
Loaded, Side Opening, #4 (7 STR) -  
3/0 (7 STR) AL, #6 (6/1) - 2/0 (6/1)  
ACSR**

By ANDERSON  
Catalog # [ADSO46N](#)

Deadend, Straight line, Spring Loaded, Side Opening, #4 (7 STR)  
- 3/0 (7 STR) AL, #6 (6/1) - 2/0 (6/1) ACSR, Conductor Range  
0.18 - 0.46 in, Fitting: None.

**Features**

Add "S" for socket or "C" for Clevis fitting options

**General**

Catalog Number	ADSO46N
Fitting Type	None
Material	Aluminum Alloy
Material - Body	356 T6 Aluminum Alloy
Material - Hardware	Galvanized Steel
Material - Keeper	356 T6 Aluminum Alloy
Material - Pin (Cotter)	Stainless Steel
Material - Socket and Clevis	Ductile Iron, Galvanized
Material - Spring (on Eyestem)	Stainless Steel
Product Category	Straight Line
Strength Rating - Ultimate	15000 lb
Body	
Style	ADS
Type	Bolted
U-Bolts	1 in
UPC	096359281245

**Dimensions**

Diameter - Bolt	0.5 in
-----------------	--------



\*Representative Image

Diameter - Pin	0.625 in
Length	6.625 in
Weight	1.2 lb
Width	0.75 in

**Conductor Related**

Conductor Diameter - Maximum	0.46
Conductor Diameter - Minimum	0.18
Conductor Diameter Range	0.18 - 0.46

**Certifications And Compliance**

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

**Logistics**

Pallet Quantity	1200
-----------------	------

**Product Assets**

[Catalogs - Distribution Connectors](#)  
[Literature - Ropes Course Industry Letter \(April 2021\)](#)  
[Sales Drawings - CC-25271](#)  
[Specifications - ADSO46N](#)