

Cable Spacer, Aluminum

By ANDERSON
Catalog # [APCS158](#)

Cable Spacer, Aluminum, 8 in Spacing, range 1.289 - 1.459 inches (1113-1272 MCM ACSR)



*Representative Image

Features

- Recommended for slack spans only
- Contact sealant is recommended

General

Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Type	Cable Spacer
UPC	096359283775

Dimensions

Dimensions	2.12 in x 9.887 in x 1.133 in
Height	1.133 in
Length	2.12 in
Weight	2.28 lb
Width	9.887 in

Conductor Related

Conductor Compatibility	ACSR-Finch-1113-54/19;ACSR-Bunting-1192.5-45/7;ACSR-Grackle-1192.5-54/19;ACSR-Bittern-1272-45/7;ACSR-Pheasant-1272-54/19;ACSR-Dipper-1351.5-45/7;ACSR-Martin-1351.5-54/19;ACSR-Bobolink-1431-45/7;AAC-Narcissus-1272-61;AAC-Columbine-1351.5-61;AAC-Carnation-1431-61;AAC-Gladiolus-1510.5-61;AAC-Coreopsis-1590-61
Conductor Diameter - Maximum	1.459 in
Conductor Diameter - Minimum	1.289 in
Conductor Diameter Range	1.289 - 1.459
Conductor Spacing	8 in
Conductor Type	<ul style="list-style-type: none">• AAC• ACSR

Logistics

Pallet Quantity	432
-----------------	-----

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - C-4936](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)