

## Cable Spacer, Aluminum

By ANDERSON  
Catalog # [APCS164](#)

Cable Spacer, Aluminum, 4 in Spacing, range 1.382 - 1.632 inches (1272-1590 MCM ACSR)



\*Representative Image

### Features

- Recommended for slack spans only
- Contact sealant is recommended

### General

Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Type	Cable Spacer
UPC	096359283805

### Dimensions

Dimensions	2.125 in x 6.063 in x 1.594 in
Height	1.594 in
Length	2.125 in
Weight	1.86 lb
Width	6.063 in

### Conductor Related

Conductor Compatibility	ACSR-Pheasant-1272-54/19;ACSR-Dipper-1351.5-45/7;ACSR-Martin-1351.5-54/19;ACSR-Bobolink-1431-45/7;ACSR-Plover-1431-54/19;ACSR-Nuthatch-1510.5-45/7;ACSR-Parrot-1510.5-54/19;ACSR-Lapwing-1590-45/7;ACSR-Falcon-1590-54/19;ACSR-Chukar-1780-84/19;AAC-Gladiolus-1510.5-61;AAC-Coreopsis-1590-61;AAC-Cowslip-2000-91
Conductor Diameter - Maximum	1.632 in
Conductor Diameter - Minimum	1.382 in
Conductor Diameter Range	1.382 - 1.632
Conductor Spacing	4 in
Conductor Type	<ul style="list-style-type: none"><li>• AAC</li><li>• ACSR</li></ul>

### Logistics

Pallet Quantity	648
-----------------	-----

### Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - C-4936](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)