

Cable Spacer, Aluminum w/ Pad

By ANDERSON
Catalog # [APCSF18D12](#)

Cable Spacer, Aluminum, 12 in Spacing, range 1.632 - 1.824 inches (2156-2312 MCM ACSR), with 4-hole, 4 in terminal



*Representative Image

Features

- Recommended for slack spans only
- Contact sealant is recommended
- For limited current use like lightning arrester tap

General

Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Type	Cable Spacer
UPC	096359500926

Dimensions

Angle - Pad	180 °
Weight	4.900 lb
Width - Pad	4 in

Conductor Related

Conductor Compatibility	ACSR-Bluebird-2156-84/19;ACSR-Kiwi-2167-72/7;ACSR-Thrasher-2312-76/19;AAC-Sagebrush-2250-91;AAC-Lupine-2500-91
Conductor Diameter - Maximum	1.824 in
Conductor Diameter - Minimum	1.632 in
Conductor Diameter Range	1.632 - 1.824
Conductor Spacing	12 in
Conductor Type	<ul style="list-style-type: none">• AAC• ACSR

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)