

**Deadend, Straight line, Spring  
Loaded, Side opening, #2 (7 STR ) -  
350 (37 STR) AL, #4 (6/1) - 336.4  
(18/1) ACSR**

By ANDERSON  
Catalog # [ASOD6841N](#)



\*Representative Image

Deadend, Straight line, Spring Loaded, Side opening, #2 (7 STR )  
- 350 (37 STR) AL, #4 (6/1) - 336.4 (18/1) ACSR, Conductor  
Range 0.25 - 0.684 in, Fitting: None.

**Features**

- Spring Loaded Vertical Keeper for Easy Installation
- Add "S" for socket or "C" for clevis fitting options

**General**

Catalog Number	ASOD6841N
Fitting Type	None
Material	Aluminum Alloy; Steel
Material - Body	356 T6 Aluminum Alloy
Material - Bolt	Galvanized Steel
Material - Hardware	Galvanized Steel
Material - Keeper	356 T6 Aluminum Alloy
Product Category	Straight Line
Strength Rating - Ultimate	8000 lb
Body	
Style	ASOD
Type	Bolted
U-Bolts	1
UPC	096359363132

**Dimensions**

Diameter - Bolt	0.5 in
Diameter - Pin	0.625 in
Length	9 in

Weight	2.03 lb
Width	0.7 in

**Conductor Related**

Conductor Diameter - Maximum	0.69
Conductor Diameter - Minimum	0.25
Conductor Diameter Range	0.25 - 0.69

**Certifications And Compliance**

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

**Logistics**

Pallet Quantity	675
-----------------	-----

**Product Assets**

[Catalog Page - ASOD Catalog Page](#)  
[Catalogs - Distribution Connectors](#)  
[Installation Manuals - ASOD\\_install instructions](#)  
[Literature - Deadends For Overhead Connections](#)  
[Literature - Ropes Course Industry Letter \(April 2021\)](#)  
[Sales Drawings - AL, Side Opening Deadend Clamp \(CC-17236\)](#)  
[Specifications - ASOD6841N](#)