

HUBBELL Power Systems

Hot Line Tap Clamp, Bronze, Inhibitor & Bag

By ANDERSON
Catalog # [BC20XB](#)

Overhead Primary Tap, Hot Line Tap Clamp, Bronze, Copper,
Range 0.128 - 0.414 in



*Representative Image

Features

High pressure developed by eyestem, lock washer assures permanent connection.

General

Catalog Number	BC20XB
Inhibitor Loaded	Yes
Material	Bronze
Material - Body	Bronze
Material - Eyebolt	Bronze
Material - Eyestem	Stainless Steel
Material - Hex Nut	Stainless Steel
Material - Keeper	Bronze
Material - Spring (on Eyestem)	Stainless Steel
Material - Washer	Stainless Steel
Plating	No
UPC	096359291152

Dimensions

Dimensions	2.625 in x 1.750 in x 5.000 in
Height	5 in
Length	2.625 in
Weight	0.715 lb
Width	1.75 in

Electrical Ratings

Maximum Current Rating Amps Continuous	Rated for maximum rating of largest tap conductor in range
--	--

Conductor Related

Conductor Diameter (Main) - Maximum	0.419 in
Conductor Diameter (Main) - Minimum	0.128 in
Conductor Diameter (Main) Range	0.128 - 0.419
Conductor Diameter (Tap) - Maximum	0.419 in
Conductor Diameter (Tap) - Minimum	0.128 in
Conductor Diameter - Maximum	0.419
Conductor Diameter - Minimum	0.128
Conductor Diameter Range	0.128 - 0.419
Conductor Type	Copper

Logistics

Carton Quantity	50
Packaging Type	Bag
Pallet Quantity	2400

Product Assets

[Catalogs - Distribution Connectors](#)
[Sales Drawings - BC20 Sales Drawing](#)
[Specifications - BC20XB](#)