

## Deadend

By ANDERSON  
Catalog # [BDE46N](#)

Deadend, Straight line, Bronze, #6 SOL - 4/0 SOL CU,  
Conductor Range 0.16- 0.46 in, Fitting: None.



\*Representative Image

### Features

- For use with copper or CopperWeld conductor
- Add "S" for socket or "C" for clevis fitting options

### General

|                                 |                  |
|---------------------------------|------------------|
| Fitting Type                    | None             |
| Material                        | Bronze; Steel    |
| Material - Body                 | Bronze Alloy     |
| Material - Bolt                 | Galvanized Steel |
| Material - Hardware             | Galvanized Steel |
| Product Category                | Straight Line    |
| Strength Rating - Ultimate Body | 6000 lb          |
| Style                           | BDE              |
| Type                            | Bolted           |
| U-Bolts                         | 2 in             |
| UPC                             | 096359291572     |

### Dimensions

|                 |          |
|-----------------|----------|
| Diameter - Bolt | 0.38 in  |
| Length          | 7.250 in |
| Weight          | 2.140 lb |
| Width           | 0.750 in |

### Conductor Related

|                              |             |
|------------------------------|-------------|
| Conductor Diameter - Maximum | 0.46        |
| Conductor Diameter - Minimum | 0.16        |
| Conductor Diameter Range     | 0.16 - 0.46 |

### Logistics

|                 |     |
|-----------------|-----|
| Pallet Quantity | 405 |
|-----------------|-----|

### Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)  
[Literature - Ropes Course Industry Letter \(April 2021\)](#)  
[Sales Drawings - Straight Deadend Strain Clamp \(C-1711\)](#)

### Related Products

[BDE60N - Deadend](#)