

Ball Eye - 30k lb

By ANDERSON
Catalog # BE30



Features

- Eye: 1.000 x 2.000" Opening x 0.688" Thick
- UTS 30,000 lb
- Material: Body is Galv. Steel
- For use with class 52-3 and 52-5 insulators per ANSI Spec. C-29.2.71

General

Catalog Number	BE30
Material	Steel
Number of Bolt Holes	0
Series	BE Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359291725

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Dimensions	2.38 in x 4.41 in x 1.69 in
Height	1.69 in
Insulator Throat Diameter - Maximum	0 in

Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length	2.38 in
Length - Coupling	3.719 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	0.98 lb
Width	4.41 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Logistics

Pallet Quantity	1920
-----------------	------

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)
[Sales Drawings - BE30 CUTSHEET](#)
[Specifications - BE30](#)