

# HUBBELL Power Systems

## Ball Eye / Shackle

By ANDERSON

Catalog # [BE30AS50](#)

Ball Eye / Shackle Assembly , Forged Steel BE30, UTS 30,000 lb (Eye: 1.000 x 2.000" Opening x 0.688" Thick) For use with ANSI class 52-3 & 52-5 insulators assembled with Forged Steel Shackle AS50, UTS 50,000 lb (0.875" Opening, 0.750" Dia. Pin).



### Features

- Forged Steel BE30: UTS 30,000 lb (Eye: 1.000 x 2.000" Opening x 0.688" Thick)
- Forged Steel Shackle AS50: UTS 50,000 lb (0.875" Opening, 0.750" Dia. Pin)
- For use with ANSI class 52-3 & 52-5 insulators
- Material: Body is Galv. Steel, Hardware is Galv. Steel & Cotter Pin is Stainless Steel

### General

EU RoHS Indicator	No
Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359291756

### Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	7.219 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	2.45 lb

### Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-BE30AS50-SPEC-EN | REV 6/2024