

# HUBBELL

## Power Systems

### Hot Line Tap Clamp, Bronze, Two Hole Pad

By ANDERSON  
Catalog # [BHF500B2](#)

Hot Line Connector with Two Hole Pad, Hot Line Tap Clamp, Bronze, Copper, Range 0.162 - 0.813 in



\*Representative Image

#### Features

2 Hole NEMA spacing for 1/2 in bolts.

#### General

Catalog Number	BHF500B2
Material	Bronze
Material - Body	Bronze
Material - Eyestem	Forged Silicon Bronze
Material - Hex Nut	Stainless Steel
Material - Keeper	Bronze
Material - Spring (on Eyestem)	Stainless Steel
Material - Washer	Stainless Steel
Plating	No
UPC	096359291879

#### Dimensions

Weight	1.666 lb
--------	----------

#### Conductor Related

Conductor Diameter (Tap) - Maximum	0.813 in
Conductor Diameter (Tap) - Minimum	0.162 in
Conductor Diameter - Maximum	0.813
Conductor Diameter - Minimum	0.162
Conductor Diameter Range	0.162 - 0.813
Conductor Type	Copper

#### Logistics

Packaging Type	Box
Pallet Quantity	1200

#### Product Assets

[Catalogs - Distribution Connectors](#)



A Hubbell brand