

Cable Spacer, Bronze

By ANDERSON  
Catalog # [BPCS1508](#)



Bronze alloy, parallel cable spacer for maintaining cable clearance and preventing loose cable damage. Recommended for slack spans only.

\*Representative Image

Features

- Bronze Cable Spacer, 8 in Spacing, range 1.152 - 1.412 inches (1000-1500 MCM)
- Recommended for slack spans only
- Material: Casting - bronze alloy, Hardware - Stainless Steel

General

Catalog Number	BPCS1508
EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Ground Braid Lug Holes	0
Type	Cable Spacer
UPC	096359292197

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	7.742 lb

Electrical Ratings

Maximum Current Rating Amps 0  
Continuous

Conductor Related

Conductor Diameter - Maximum	1.412 in
Conductor Diameter - Minimum	1.152 in
Conductor Diameter Range	1.152 - 1.412
Conductor Spacing	8 in
Conductor Type	Copper

Certifications And Compliance

Buy America(n) Qualified      Contact Manufacturer

Product Assets

- [Catalogs - Substation Connectors \(SA\)](#)
- [Sales Drawings - C-12901 \(BPCS Product Family\)](#)
- [Specifications - BPCS1508](#)
- [Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products](#)
- [Video - Hubbell Power Systems Quick Ship](#)