

Deadend

By ANDERSON
Catalog # [BSC050N](#)

Deadend, Straight line, Bronze, 4/0 STR - 550 MCM CU,
Conductor Range 0.52- 0.875 in, Fitting: None.



*Representative Image

Features

- For use with copper or CopperWeld conductor
- Add "S" for socket or "C" for clevis fitting options

General

EU RoHS Indicator	Contact Manufacturer
Fitting Type	None
Material	Aluminum-Bronze Alloy; Steel
Material - Body	Bronze Alloy
Material - Bolt	Galvanized Steel
Material - Hardware	Galvanized Steel
Product Category	Straight Line
Strength Rating - Ultimate Body	8000 lb
Style	BSC
Type	Bolted
U-Bolts	2 in
UPC	096359292562

Dimensions

Diameter - Bolt	0.5 in
Weight	3.720 lb

Conductor Related

Conductor Diameter - Maximum	0.875
Conductor Diameter - Minimum	0.52
Conductor Diameter Range	0.52 - 0.875

Logistics

Pallet Quantity	420
-----------------	-----

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - Bronze Strain Clamp \(C-2724\)](#)

Related Products

[BSC100N - Deadend](#)
[BSC024N - Deadend](#)