

HUBBELL Power Systems

Deadend

By ANDERSON
Catalog # [BSC100N](#)

Deadend, Straight line, Bronze, 500 - 1000 MCM CU, Conductor
Range 0.81- 1.25 in, Fitting: None.



*Representative Image

Features

- For use with copper or CopperWeld conductor
- Add "S" for socket or "C" for clevis fitting options

General

Catalog Number	BSC100N
EU RoHS Indicator	Contact Manufacturer
Fitting Type	None
Material	Aluminum-Bronze Alloy; Steel
Material - Body	Bronze Alloy
Material - Bolt	Galvanized Steel
Material - Hardware	Galvanized Steel
Product Category	Straight Line
Strength Rating - Ultimate	10000 lb
Body	
Style	BSC
Type	Bolted
U-Bolts	3 in
UPC	096359292593

Dimensions

Diameter - Bolt	0.5 in
Weight	6.76 lb

Conductor Related

Conductor Diameter - Maximum	1.25
Conductor Diameter - Minimum	0.81
Conductor Diameter Range	0.81 - 1.25

Product Assets

[Catalogs - Distribution Connectors](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - Bronze Strain Clamp \(C-2724\)](#)



A Hubbell brand