

Deadend

By ANDERSON
Catalog # [BSG050N](#)

Deadend, Compact design, Straight line, Bronze, 2/0 SOL - 550
MCM CU, Conductor Range .36 - 875 in, Fitting: None



*Representative Image

Features

- For use with copper or CopperWeld conductor
- Ideal for pole type substations and other short span dead ending, Add "S" for socket or "C" for clevis fitting options

General

Catalog Number	BSG050N
EU RoHS Indicator	Contact Manufacturer
Fitting Type	None
Material	Aluminum-Bronze Alloy; Steel
Material - Body	Bronze Alloy
Material - Bolt	Galvanized Steel
Material - Hardware	Galvanized Steel
Material - Hex Nut	Silicon Bronze
Number of Bolt Holes	4
Product Category	Straight Line
Strength Rating - Ultimate	5500 lb
Body	
Style	BSG
Type	Bolted

UPC 096359292883

Dimensions

Diameter - Bolt	0.5 in
Weight	3.43 lb

Conductor Related

Conductor Diameter - Maximum	0.875
Conductor Diameter - Minimum	0.36
Conductor Diameter Range	0.36 - 0.875

Logistics

Pallet Quantity	420
-----------------	-----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Sales Drawings - Bronze Strain Clamp Type-BSG \(C-2791\)](#)
- [Specifications - BSG050N](#)