

Deadend

By ANDERSON
Catalog # [BSG100N](#)

Deadend, Compact design, Straight line, Bronze, 500 mcm - 1000 MCM CU, Conductor Range .81 - 1.25 in, Fitting: None



*Representative Image

Features

- For use with copper or CopperWeld conductor
- Ideal for pole type substations and other short span dead ending, Add "S" for socket or "C" for clevis fitting options

General

EU RoHS Indicator	Contact Manufacturer
Fitting Type	None
Material	Aluminum-Bronze Alloy; Steel
Material - Body	Bronze Alloy
Material - Bolt	Galvanized Steel
Material - Hardware	Galvanized Steel
Material - Hex Nut	Silicon Bronze
Number of Bolt Holes	4
Product Category	Straight Line
Strength Rating - Ultimate Body	7500 lb
Style	BSG
Type	Bolted
UPC	096359292913

Dimensions

Diameter - Bolt	0.5 in
Length	7.500 in
Weight	4.700 lb
Width	0.688 in

Conductor Related

Conductor Diameter - Maximum	1.25
Conductor Diameter - Minimum	0.81
Conductor Diameter Range	0.81 - 1.25

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - Bronze Strain Clamp Type-BSG \(C-2791\)](#)

Related Products

[BSG050N - Deadend](#)