

## Deadend, Straight line, Spring Loaded, Bronze, Side opening, #6 SOL - 4/0 (19 STR) CU

By ANDERSON  
Catalog # [BSOD5701N](#)

Deadend, Straight line, Spring Loaded, Bronze, Side opening, #6 SOL - 4/0 (19 STR) CU, Conductor Range 0.16 - 0.57 in, Fitting: None.



\*Representative Image

### Features

- Spring Loaded Vertical Keeper for Easy Installation

### General

Fitting Type	None
Material	Bronze; Steel
Material - Body	Bronze Alloy
Material - Bolt	Galvanized Steel
Material - Hardware	Galvanized Steel
Product Category	Straight Line
Strength Rating - Ultimate Body	8000 lb
Style	BSOD
Type	Bolted
U-Bolts	2 in
UPC	096359453895

### Dimensions

Diameter - Bolt	0.5 in
Length	8.620 in
Weight	3.750 lb
Width	1.000 in

### Conductor Related

Conductor Diameter - Maximum	0.57
Conductor Diameter - Minimum	0.16
Conductor Diameter Range	0.16 - 0.57

### Logistics

Pallet Quantity	480
-----------------	-----

### Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)  
[Literature - Ropes Course Industry Letter \(April 2021\)](#)  
[Sales Drawings - Bronze, Side Opening Deadend Clamp \(CC-19130\)](#)