

**Clevis Eye, Rotated 90-deg**

By ANDERSON  
Catalog # [CE02513](#)

Type CE Clevis Eyes are used to connect quadrant type deadends to clevis tongue insulators or yoke plates. The eye type CE is 90° from type CA. Material: body - galvanized ductile iron, clevis pin - galvanized steel, cotter pin - stainless steel.



\*Representative Image

**Features**

"BNK" suffix if added replaces clevis pin & cotter pin with bolt, nut & cotter pin

**General**

|                                 |                  |
|---------------------------------|------------------|
| Catalog Number                  | CE02513          |
| EU RoHS Indicator               | No               |
| Material                        | Ductile Iron     |
| Material - Pin (Clevis)         | Galvanized Steel |
| Material - Pin (Cotter)         | Stainless Steel  |
| Number of Bolt Holes            | 0                |
| Series                          | CE Series        |
| Strength Rating - Ultimate      | 25000 lb         |
| Strength Rating - Ultimate Body | 0 lb             |
| UPC                             | 096359298328     |

**Dimensions**

|                                     |          |
|-------------------------------------|----------|
| Assembly Rating (Ultimate)          | 0 lb     |
| Diameter - Bolt                     | 0 in     |
| Diameter - Eye Hole                 | 0.688 in |
| Diameter - Pin                      | 0 in     |
| Insulator Throat Diameter - Maximum | 0 in     |
| Insulator Throat Diameter - Minimum | 0 in     |

|                                 |          |
|---------------------------------|----------|
| Insulator Throat Diameter Range | 0 - 0    |
| Length - Coupling               | 2.625 in |
| Length - Pin                    | 0 in     |
| Maximum Adjustment              | 0 in     |
| Ring Height                     | 0 in     |
| Weight                          | 2.156 lb |
| Width - Eye                     | 1.375 in |

**Conductor Related**

|                              |      |
|------------------------------|------|
| Conductor Diameter - Maximum | 0 in |
| Conductor Spacing            | 0 in |

**Certifications And Compliance**

|                          |   |
|--------------------------|---|
| Buy America(n) Qualified | TAA Compliant (All status valid till December 2024) |
|--------------------------|---|

**Logistics**

|                 |     |
|-----------------|-----|
| Pallet Quantity | 960 |
|-----------------|-----|

**Product Assets**

[Catalogs - Transmission Connectors Catalog - Full](#)  
[Sales Drawings - C-11403](#)  
[Specifications - CE02513](#)