

Clevis Eye, Rotated 90-deg

By ANDERSON
Catalog # [CE03305](#)

Type CE Clevis Eyes are used to connect quadrant type deadends to clevis tongue insulators or yoke plates. The eye type CE is 90° from type CA. Material: body - galvanized ductile iron, clevis pin - galvanized steel, cotter pin - stainless steel.

Features

"BNK" suffix if added replaces clevis pin & cotter pin with bolt, nut & cotter pin

General

Catalog Number	CE03305
Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	CE Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359298342

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Eye Hole	0.688 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in



Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	3.375 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	2.221 lb
Width - Eye	0.5 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Logistics

Pallet Quantity	1200
-----------------	------

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)
[Sales Drawings - CE-033-05 CUTSHEET](#)
[Specifications - CE03305](#)