

Clevis Eye, Rotated 90-deg

By ANDERSON
Catalog # [CE05410](#)

Clevis Eye, Rotated, Ductile Iron, Clevis: 1.000" Opening,
0.750" Pin, Eye: 1.000" width w/ 0.813" Hole, UTS 40,000 lb



*Representative Image

Features

- "BNK" suffix if added replaces clevis pin & cotter pin with bolt, nut & cotter pin

General

EU RoHS Indicator	No
Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Series	CE Series
Strength Rating - Ultimate	40000 lb
UPC	096359298434

Dimensions

Diameter - Eye Hole	0.813 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	5.5 in
Weight	3.136 lb
Width - Eye	1 in

Logistics

Pallet Quantity	720
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)