

## Clevis-Eye, Wide, Rotated 90-deg

By ANDERSON  
Catalog # [CEW13530](#)

Clevis Eye, Wide Clevis, Ductile Iron, Clevis: 2.000" Opening, 0.625" Pin, Eye: 1.438" with 0.688" Hole, UTS 30,000 lb



\*Representative Image

### Features

- "BNK" suffix if added replaces clevis pin & cotter pin with bolt, nut & cotter pin

### General

EU RoHS Indicator	No
Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Series	CEW Series
Strength Rating - Ultimate	30000 lb
UPC	096359298687

### Dimensions

Diameter - Eye Hole	0.688 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	2.875 in
Weight	2.548 lb
Width - Eye	1.438 in

### Logistics

Carton Quantity	20
-----------------	----

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)