

Stud Connector, Bronze

By ANDERSON
Catalog # [DS1105012](#)

"Bolted Stud Connectors, Connecting Stud to Cable, Stud Dia./Thd.-1-1/8"-12, Copper Conductor Range- Cable-#4-Sol.-250-MCM, Dia-0.204"-0.575", Material: Castings-Bronze Alloy, Hardware-Silicon Bronze or Stainless Steel"



*Representative Image

Features

- 0

General

EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Stud Threads	12
Type	Stud to Tube or Cable
UPC	096359300151

Dimensions

Diameter - Stud	1.125 in
Weight	3.136 lb

Conductor Related

Conductor Diameter - Maximum	0.813 in
Conductor Diameter - Minimum	0.162 in
Conductor Diameter Range	0.162 - 0.813
Conductor Type	Copper

Logistics

Pallet Quantity	504
-----------------	-----

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - CC-1487 \(DS Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)