

Stud Connector, Bronze

By ANDERSON
Catalog # [DSC140509012](#)

"Bolted Stud Connectors, Connecting Stud to Cable, Stud Dia./Thd.-3"-12, Copper Conductor Range- Cable- 4/0 Str.-1000 MCM,Dia-0.522"-1.152", Material: Castings-Bronze Alloy, Hardware-Silicon Bronze or Stainless Steel"



*Representative Image

Features

- "All sizes furnished with reversible cable caps"

General

EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Stud Threads	12
Type	Stud to Cable
UPC	096359300786

Dimensions

Angle - Stud to Conductor	90 °
Diameter - Stud	1.5 in
Weight	4.900 lb

Conductor Related

Conductor Diameter - Maximum	0.813 in
Conductor Diameter - Minimum	0.325 in
Conductor Diameter Range	0.325 - 0.813
Conductor Type	Copper

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - C-2888 \(DSC Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)