

Hot Line Link, Clevis Clevis

By ANDERSON  
Catalog # [FHCC30L90](#)



Hot Line Clevis Clevises are forged from high strength steel and contain no welded joints. Because of the variety of fittings and lengths, links are made only to order. Please specify by catalog number and the length required.

Features

- Hot Line Clevis Clevis: 0.938" x 2.375" Opening x 0.750" Thick
- Clevis: 0.813" Opening x 0.625" Pin
- UTS 30,000 lb
- Material: Body-Galvanized Forged steel, Clevis Pin-Galvanized steel, Cotter pin-Stainless steel
- Available Range of Lengths: Minimum-12" Maximum-144" with .500" increment
- Use letter "D" to represent decimal point in catalog number when applicable

General

Catalog Number	FHCC30L90
Coupling Orientation	Rotated
Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Number of Bolt Holes	0
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate Body	0 lb

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Specifications - FHCC30L90](#)