

## Hot Line Link, Clevis Clevis

By ANDERSON  
Catalog # [FHCC50L](#)

"Hot Line Oval-Eye Clevis, Rotated, Oval Eye: 0.938" x 2.375"  
Opening x 0.750" Thick; Clevis: 0.813" Opening x 0.625" Pin ,  
UTS 30,000 lb"



### Features

- "Material: Body-Galvanized Forged steel, Clevis Pin-Galvanized steel, Cotter pin-Stainless steel
- Available Range of Lengths: Minimum-12" Maximum-144" with .500" increment
- Use letter "D" to represent decimal point in catalog number when applicable Example: FHCC5012D5 for 12.500" length
- Bolt and nut may be substituted for clevis pin by adding suffix "BNK" to catalog number
- Shield nut can be supplied by adding suffix "SN" to catalog number"

### General

Coupling Orientation	Straight
Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Strength Rating - Ultimate	50000 lb

### Dimensions

Insulator Throat Diameter      0 - 0  
Range

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)