

Hot Line Link, Oval-Eye Clevis

By ANDERSON
Catalog # [FHOEC50L90](#)

"Hot Line Link, Socket Eye. Eye: 0.750" Thick. With 0.813" Dia.
Hole UTS 30,000 lb"



*Representative Image

Features

- "Material: Body-Galvanized Forged steel, Clevis Pin-Galvanized steel, Cotter pin-Stainless steel
- Available Range of Lengths: Minimum-11" Maximum-144" with 0.500" increment
- Use letter "D" to represent decimal point in catalog number when applicable Example: FHOEC5012D590 for 12.500" length
- Bolt and nut may be substituted for clevis pin by adding suffix "BNK" to catalog number
- Shield nut can be supplied by adding suffix "SN" to catalog number"

General

Coupling Orientation	Rotated
Extension Link Type	Oval-Eye Clevis
Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Strength Rating - Ultimate	50000 lb

Dimensions

Insulator Throat Diameter 0 - 0
Range

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)