

HUBBELL Power Systems

Hot Line Link, Y-Clevis Eye

By ANDERSON

Catalog # [FHYCE30L](#)

Hot Line Y-Clevis Eyes are forged from high strength steel and contain no welded joints. Because of the variety of fittings and lengths, links are made only to order. Please specify by catalog number and the length required.



Features

- Hot Line Clevis Eye, Clevis: 1.000" Opening, Clevis pin: 0.625", Eye: 0.625" Thick. 0.688" Hole
- UTS 30,000 lb
- Material: Body-Galvanized Forged steel, Bent bolt & Hex. Nut-Galvanized steel, Cotter pin-Stainless steel
- Available Range of Lengths: Minimum-11" Maximum-144" with 0.500" increment
- Use letter "D" to represent decimal point in catalog number when applicable Example: FHYCE3012D5 for 12.500" length
- Shield nut can be supplied by adding suffix "SN" to catalog number"

General

Coupling Orientation	Straight
Extension Link Type	Y-Clevis Eye
Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Number of Bolt Holes	0
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate Body	0 lb

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Eye Hole	0.688 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Width - Eye	0.563 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-FHYCE30L-SPEC-EN | REV 6/2024