

Hot Line Link, Y-Clevis Eye

By ANDERSON
Catalog # [FHYCE30L90](#)

Hot Line Y-Clevis Eyes are forged from high strength steel and contain no welded joints. Because of the variety of fittings and lengths, links are made only to order. Please specify by catalog number and the length required.

Features

- Hot Line Clevis Eye, Clevis Rotated: 1.000" Opening, Clevis pin: 0.625", Eye: 0.625" Thick. 0.688" Hole
- UTS 30,000 lbMaterial: Body-Galvanized Forged steel, Bent bolt & Hex. Nut-Galvanized steel, Cotter pin-Stainless steel
- Available Range of Lengths: Minimum-11" Maximum-144" with 0.500" increment
- Use letter "D" to represent decimal point in catalog number when applicable Example: FHYCE3012D5 for 12.500" length
- Shield nut can be supplied by adding suffix "SN" to catalog number"

General

| | |
|---------------------------------|------------------|
| Catalog Number | FHYCE30L90 |
| Coupling Orientation | Rotated |
| Extension Link Type | Y-Clevis Eye |
| Material | Steel |
| Material - Pin (Clevis) | Galvanized Steel |
| Number of Bolt Holes | 0 |
| Strength Rating - Ultimate | 30000 lb |
| Strength Rating - Ultimate Body | 0 lb |

Dimensions

| | |
|-------------------------------------|----------|
| Assembly Rating (Ultimate) | 0 lb |
| Diameter - Bolt | 0 in |
| Diameter - Eye Hole | 0.688 in |
| Diameter - Pin | 0 in |
| Insulator Throat Diameter - Maximum | 0 in |
| Insulator Throat Diameter - Minimum | 0 in |
| Insulator Throat Diameter Range | 0 - 0 |
| Length - Pin | 0 in |
| Maximum Adjustment | 0 in |
| Ring Height | 0 in |
| Width - Eye | 0.563 in |

Conductor Related

| | |
|------------------------------|------|
| Conductor Diameter - Maximum | 0 in |
| Conductor Spacing | 0 in |

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Specifications - FHYCE30L90](#)

