

Hot Line Link, Oval-Eye Eye

By ANDERSON
Catalog # [FOPE30L90](#)

Hot Line Chain Eye Eyes are forged from high strength steel and contain no welded joints. Because of the variety of fittings and lengths, links are made only to order. Please specify by catalog number and the length required.

Features

- Hot Line Link, Oval-Eye Eye Rotated: 1.060" Thick. With 1.060" Dia. Hole
- UTS 30,000 lbMaterial: Body-Galvanized Forged steel, Bent bolt & Hex. Nut-Galvanized steel, Cotter pin-Stainless steel
- Available Range of Lengths: Minimum-11" Maximum-144" with 0.500" increment
- Use letter "D" to represent decimal point in catalog number when applicable Example: FHYCE3012D5 for 12.500" length
- Shield nut can be supplied by adding suffix "SN" to catalog number"

General

Catalog Number	FOPE30L90
Coupling Orientation	Rotated
Extension Link Type	Oval-Eye Eye
Material	Steel
Number of Bolt Holes	0
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate Body	0 lb

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Eye Hole	0.688 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Width - Eye	0.563 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Specifications - FOPE30L90](#)

