

## Compression Splice Full Tension

By ANDERSON  
Catalog # [FTA397](#)

Full Tension Aluminum splice for 397.5 (19 STR) AAC



\*Representative Image

### Features

- Has positive center stop and tapered ends.

### General

Compression Method	Conventional Die Tooling
Die Size	Burndy 468, 655 or EEI-13A
EU RoHS Indicator	Contact Manufacturer
Inhibitor Loaded	Yes
Material	Aluminum Alloy
UPC	096359303817

### Dimensions

Length Before Compression	12.25 in
Weight	0.784 lb

### Conductor Related

Conductor Compatibility	AAC-Tulip-336.1-19;AAC-Daffodil-350-19
Conductor Diameter - Maximum	0.724
Conductor Diameter - Minimum	0.659
Conductor Diameter Range	0.659 - 0.724

### Certifications and Compliance

UL Listed	No
-----------	----

### Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)