

Compression SpliceFull Tension

By ANDERSON
Catalog # [FTR336](#)



Full Tension Aluminum splice for 336.4 (18/1) ACSR, 336.4 (19 STR) AAC

*Representative Image

Features

Has positive center stop and tapered ends.

General

Catalog Number	FTR336
Compression Method	Conventional Die Tooling
Die Size	Burndy 655 or EEI-13A
EU RoHS Indicator	Contact Manufacturer
Inhibitor Loaded	Yes
Material	Aluminum Alloy
UPC	096359303879

Dimensions

Length Before Compression	19.25 in
Weight	1.372 lb

Conductor Related

Conductor Compatibility	ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;AAC-Tulip-336.1-19;AAC-Daffodil-350-19
Conductor Diameter - Maximum	0.684
Conductor Diameter - Minimum	0.607
Conductor Diameter Range	0.607 - 0.684

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
UL Listed	No

Product Assets

[Catalogs - Distribution Connectors](#)
[Specifications - FTR336](#)