

Compression SpliceFull Tension

By ANDERSON  
Catalog # [FTR40](#)



Full Tension Aluminum splice for 4/0 (6/1) ACSR, 4/0 (7 STR) AAAC, and 4/0 (7 STR) AAC

\*Representative Image

Features

Has positive center stop and tapered ends.

General

Catalog Number	FTR40
Compression Method	Conventional Die Tooling
Die Size	Burndy 654 or EEI-12A
EU RoHS Indicator	Contact Manufacturer
Inhibitor Loaded	Yes
Material	Aluminum Alloy
UPC	096359303909

Dimensions

Length Before Compression	18.5 in
Weight	1.176 lb

Conductor Related

Conductor Compatibility	ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;AAC-Oxlip-4/0-7;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18
Conductor Diameter - Maximum	0.565
Conductor Diameter - Minimum	0.48
Conductor Diameter Range	0.48 - 0.565

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
UL Listed	No

Product Assets

[Catalogs - Distribution Connectors](#)  
[Specifications - FTR40](#)