

## Grounding Clamp

By ANDERSON  
Catalog # [GC10904](#)

"Grounding Clamp, Bronze Bolted, Copper One, Two, or Three Cable to Rod or Tube Parallel, U-bolt style, Cables Dia. Range 0.574"-0.813" to 4-1/2" OD Rod or 4" EHIPS Tube, Material: Casting-Bronze alloy, Hardware-Silicon Bronze or Stainless steel"



\*Representative Image

### Features

- "Use with GB Cu Braid
- Everdur hardware supplied by adding Suffix "ED" e.g.GC10904ED
- Tin Plated by adding Suffix "TP" e.g.GC10904TP"

### General

|                     |                 |
|---------------------|-----------------|
| EU RoHS Indicator   | No              |
| Material            | Bronze          |
| Material - Hardware | Stainless Steel |
| UPC                 | 096359305392    |

### Dimensions

|                               |          |
|-------------------------------|----------|
| Diameter - Clamping Hardware  | 1 in     |
| Diameter - Rod / Tube         | 1 in     |
| Diameter - Rod / Tube Outside | 1.25 in  |
| Weight                        | 0.588 lb |

### Conductor Related

|                |        |
|----------------|--------|
| Conductor Type | Copper |
|----------------|--------|

### Product Assets

[Sales Drawings - C-11337 \(GC109 Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)