

Grounding Clamp

By ANDERSON
Catalog # [GC10904](#)

"Grounding Clamp, Bronze Bolted, Copper One, Two, or Three Cable to Rod or Tube Parallel, U-bolt style, Cables Dia. Range 0.574"-0.813" to 4-1/2" OD Rod or 4" EHIPS Tube, Material: Casting-Bronze alloy, Hardware-Silicon Bronze or Stainless steel"



*Representative Image

Features

- "Use with GB Cu Braid
- Everdur hardware supplied by adding Suffix "ED" e.g.GC10904ED
- Tin Plated by adding Suffix "TP" e.g.GC10904TP"

General

EU RoHS Indicator	No
Material	Bronze
Material - Hardware	Stainless Steel
UPC	096359305392

Dimensions

Diameter - Clamping Hardware	1 in
Diameter - Rod / Tube	1 in
Diameter - Rod / Tube Outside	1.25 in
Weight	0.588 lb

Conductor Related

Conductor Type	Copper
----------------	--------

Product Assets

[Sales Drawings - C-11337 \(GC109 Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)