

Grounding Clamp

By ANDERSON
Catalog # [GC11042D](#)

"Grounding Clamp, Bronze Bolted, Copper Cable to Rod or Tube, U-bolt style, Cables Range 0.204"-0.419" dia. to 1/2"-3/4" OD Rod or 1/4"-3/8" EHIPS Tube, Material: Casting-Bronze alloy, Hardware-Silicon Bronze or Stainless steel"



*Representative Image

Features

- "Everdur hardware supplied by adding Suffix "ED" e.g.GC11042DED"

General

EU RoHS Indicator	No
Material	Bronze
Material - Hardware	Stainless Steel
UPC	096359350941

Dimensions

Diameter - Clamping Hardware	1 in
Diameter - Rod / Tube	1 in
Diameter - Rod / Tube Outside	1.25 in
Weight	1.078 lb

Conductor Related

Conductor Diameter - Maximum	0.575 in
Conductor Diameter - Minimum	0.365 in
Conductor Diameter Range	0.365 - 0.575
Conductor Type	Copper

Product Assets

[Sales Drawings - C-2336 \(GC-110 and AGC-110 Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)