

Grounding Clamp

By ANDERSON
Catalog # [GC11061C](#)

"Grounding Clamp, Bronze Bolted, Copper Cable to Rod or Tube, U-bolt style, Cables Range 0.204"-0.419" dia. to 5/8"-1" OD Rod or 3/8"-3/4" EHIPS Tube, Material: Casting-Bronze alloy, Hardware-Silicon Bronze or Stainless steel"



*Representative Image

Features

- "Everdur hardware supplied by adding Suffix "ED" e.g.GC11061CED"

General

Material	Bronze
Material - Hardware	Stainless Steel
UPC	096359305651

Dimensions

Diameter - Clamping Hardware	1.5 in
Diameter - Rod / Tube	1.5 in
Diameter - Rod / Tube Outside	2 in
Dimensions	3.314 in x 1.5 in x 0.563 in
Height	0.563 in
Length	3.314 in
Weight	1.254 lb
Width	1.5 in

Conductor Related

Conductor Diameter - Maximum	0.419 in
Conductor Diameter - Minimum	0.204 in
Conductor Diameter Range	0.204 - 0.419
Conductor Type	Copper

Logistics

Pallet Quantity	1080
-----------------	------

Product Assets

[Catalogs - Substation Connectors Combined \(CA05044E\)](#)
[Sales Drawings - C-2336](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)