

Grounding Clamp

By ANDERSON
Catalog # [GC11062C](#)

"Grounding Clamp, Bronze Bolted, Copper Cable to Rod or Tube, U-bolt style, Cables Range 0.365"-0.575" dia. to 5/8"-1" OD Rod or 3/8"-3/4" EHIPS Tube, Material: Casting-Bronze alloy, Hardware-Silicon Bronze or Stainless steel"



*Representative Image

Features

- "Everdur hardware supplied by adding Suffix "ED" e.g.GC11062CED"

General

Material	Bronze
Material - Hardware	Stainless Steel
UPC	096359305668

Dimensions

Diameter - Clamping Hardware	1.5 in
Diameter - Rod / Tube	1.5 in
Diameter - Rod / Tube Outside	2 in
Weight	1.176 lb

Conductor Related

Conductor Diameter - Maximum	0.575 in
Conductor Diameter - Minimum	0.365 in
Conductor Diameter Range	0.365 - 0.575
Conductor Type	Copper

Logistics

Pallet Quantity	1008
-----------------	------

Product Assets

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)