

Grounding Clamp

By ANDERSON
Catalog # [GC1115CTP](#)

"Grounding Clamp, Bronze Bolted, Copper Cable to Cable, Cross Connector, U-bolt style, Cable Range Main, Tap 2/0 Sol.-250 MCM, Material: Casting-Bronze alloy, Hardware-silicon bronze or stainless steel"



*Representative Image

Features

- "Tin plating will be supplied "

General

EU RoHS Indicator	No
Material	Bronze
Material - Hardware	Stainless Steel
UPC	096359305996

Dimensions

Diameter - Clamping Hardware	1.25 in
Diameter - Rod / Tube	1.25 in
Diameter - Rod / Tube Outside	1.75 in
Weight	1.568 lb

Conductor Related

Conductor Diameter - Maximum	0.575 in
Conductor Diameter - Minimum	0.365 in
Conductor Diameter Range	0.365 - 0.575
Conductor Type	Copper

Logistics

Pallet Quantity	864
-----------------	-----

Product Assets

- [Sales Drawings - C-2951 \(GC111 Product Family\)](#)
- [Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)
- [Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)

